



CHICAGO PUMPS

DRY-PIT SUBMERSIBLE PUMP

ORDER FORM

Yeomans Chicago Corporation
3905 Enterprise Ct
Aurora, IL
USA
60504
Phone: 630-236-5500
Fax: 630-236-5511
www.yccpump.com

Date: PO#

Sold-To

Company:

Address1:

Address2:

City:

State/Province:

Zip/Postal Code:

Contact Name:

Phone:

Ship-to

Same as Sold-To

Company:

Address1:

Address2:

City:

State/Province:

Zip/Postal Code:

Contact Name:

Phone:

Job Status

Shipping Notes or Reference

Freight Terms - Note: FOB Factory (Standard)

Freight Terms

Note: "To Be Advised" as a ship-to address will only be allowed for YCC to enter the order in the system - Please provide a valid ship-to so we may release to production

Job Name / End-User O&M Manual Preliminary QTY Final QTY

Industry Application / Usage

Note: O&M's Not Applicable on Buy & Resell orders - Reps are to call YCC for e-mail copy of the Generic Pump Manual - Manuals per Spec will require an adder

YCC QUOTE# Customer Requested Date Std. Lead-Time (target date)

Note: Dates are just an estimated ship date. All Standard Lead-time depends on stock & supplier delivery - Please call YCC for accurate ship dates

QTY	PUMP INFORMATION	Unit Price	Amount
	Series <input type="text"/> Model <input type="text"/>		
	Duty Point: GPM <input type="text"/> @ TDH (feet) <input type="text"/> Or Impeller Dia. <input type="text"/>		
	Rotation / Position <input type="text"/>		
	Suction Inceaser <input type="text"/>		
PUMP OPTIONS			
	Suction Wear-Ring <input type="text"/>		
	Impeller Wear-Ring <input type="text"/>		
	Imp. Material: <input type="text"/>		
	Paint: <input type="text"/>		
MOTOR INFORMATION			
	<input type="text"/> HP <input type="text"/> RPM <input type="text"/> Volts <input type="text"/> Phase <input type="text"/> Hertz <input type="text"/> Frame <input type="text"/>		
	Cable Length <input type="text"/> Inverter Duty NEMA MG1,Part 31 <input type="text"/>		
FACTORY TESTING			
	Performance Test <input type="text"/>		
	Curve Approval before Shipment <input type="text"/>		
	Certified Hydro Test <input type="text"/>		
	Certified Megger Test <input type="text"/> Approval before Shipment <input type="text"/>		

YCC allows a maximum of 2 weeks for review and acceptance

OPTIONAL EQUIPMENT / ACCESSORIES / ADDITIONAL EQUIPMENT

Special Notes

Multiplier (entry in decimals)

	Total List Price	
	Total Net Price	
	Start-Up	
	Other Spcl. Notes	
	Tax	
	FREIGHT	
	Grand Total	

Commission Amt.

YCC Notations:

1. Freight shipments requiring liftgate service or open top/flat bed truck are NOT standard freight. These services are available at extra cost, which must be included at time of order entry. Consult YCC for special pricing. Reconsignment fees and liftgate service fees will be applied if this is done after carrier pick-up at YCC. Refer to price book page viii "Truck Shipment - Tariff Pricing" for additional information.
2. Terms of Payment: Payment is due upon shipment or invoice unless agreed in advance and in writing.
3. Upon request generic O&M manuals in PDF locked format, or in printed form in quantity of 3 or less, may be transmitted on or before ship date at no charge. Add \$95.00 net each for printed generic O&M manuals in quantities greater than 3. Project specific manuals in printed or electronic form are subject to additional charges as determined by YCC.
4. Pump duty point must be specified if performance testing is required.
5. Final impeller trim diameter will be determined by YCC
6. All YCC Orders will be manufactured using the most current design standards unless noted otherwise

FOR INTERNAL USE ONLY

Reviewed by	<input style="width: 150px;" type="text"/>
Product Code	<input style="width: 150px;" type="text"/>
Credit Approval	<input style="width: 150px;" type="text"/>
Rep Code	<input style="width: 150px;" type="text"/>

Entered By:

Title: