

Frame Mounted End Suction Fire Pumps



Peerless Pump Company

2005 Dr. Martin Luther King Jr. Street
Indianapolis, IN 46202
Phone: (317) 925-9661 • Fax: (317) 924-7388

US Gpm	Head		Pump Model	Shut-off Head Feet	Shut -Off Head Psi	Speed Rpm	Pump Max Bhp	UL Listed Motor Drive Bhp with 1.15 Serv. Fact. or UL Listed for Engine Drive	ULC Listed Motor Drive Bhp with 1.15 Serv. Fact. or ULC Listed for Engine	FM Approved Motor Drive Bhp with 1.15 Serv. Fact. or FM Approved for Engine	Type Driver
	Psi	Feet									
200	40	92	3UNF7	125	54	3500	19.0	20	N.A.	20	MOTOR
200	52	120	3UNF8	170	74	2950	30.0	30	N.A.	30	MOTOR
200	55	127	2.5UNF8	130	56	2950	20.0	20	N.A.	20	MOTOR
200	67	155	3UNF7	190	82	3500	27.0	25	N.A.	25	MOTOR
200	70	162	2UNF10	190	82	2600	21.0	YES	N.A.	YES	ENGINE
200	81	187	3UNF8	275	119	2950	42.0	40	N.A.	40	MOTOR
200	93	215	2UNF10	240	104	2950	30.0	30	N.A.	30	MOTOR
200	101	233	2.5UNF8	237	103	2950	53.0	50	N.A.	50	MOTOR
200	112	259	2UNF10	270	117	2600	38.0	YES	N.A.	YES	ENGINE
200	148	342	2UNF10	355	154	2950	56.0	50	N.A.	50	MOTOR
250	50	116	3UNF7	125	54	3500	19.0	20	N.A.	20	MOTOR
250	51	118	3UNF8	170	74	2950	30.0	30	N.A.	30	MOTOR
250	55	127	2.5UNF8	130	56	2950	20.0	20	N.A.	20	MOTOR
250	77	178	3UNF7	190	82	3500	27.0	25	N.A.	25	MOTOR
250	78	180	3UNF8	275	119	2950	42.0	40	N.A.	40	MOTOR
250	88	203	2UNF10	240	104	2950	30.0	30	N.A.	30	MOTOR
250	90	208	2UNF10	190	82	2600	21.0	YES	N.A.	YES	ENGINE
250	101	233	2.5UNF8	237	103	2950	53.0	50	N.A.	50	MOTOR
250	108	249	2UNF10	270	117	2600	38.0	YES	N.A.	YES	ENGINE
250	142	328	2UNF10	355	154	2950	56.0	50	N.A.	50	MOTOR
300	48	111	3UNF7	125	54	3500	19.0	20	N.A.	20	MOTOR
300	49	113	3UNF8	170	74	2950	30.0	30	N.A.	30	MOTOR
300	52	120	2.5UNF8	130	56	2950	20.0	20	N.A.	20	MOTOR
300	55	127	3UNF11	133	58	2350	21.8	YES	N.A.	YES	ENGINE
300	60	139	3UNF11	150	65	2350	26.0	YES	N.A.	YES	ENGINE
300	65	150	3UNF11	163	70	2350	29.5	YES	N.A.	YES	ENGINE
300	69	159	3UNF11	165	71	2600	29.0	YES	N.A.	YES	ENGINE
300	70	162	3UNF11	170	74	2350	35.1	YES	N.A.	YES	ENGINE
300	75	173	3UNF11	179	78	2350	37.9	YES	N.A.	YES	ENGINE
300	75	173	3UNF11	178	77	2600	30.0	YES	N.A.	YES	ENGINE
300	75	173	3UNF7	190	82	3500	27.0	25	N.A.	25	MOTOR
300	76	176	3UNF8	275	119	2950	42.0	40	N.A.	40	MOTOR
300	80	185	3UNF11	194	84	2350	42.4	YES	N.A.	YES	ENGINE
300	80	185	3UNF11	194	84	2600	39.0	YES	N.A.	YES	ENGINE
300	80	185	3UNF11	198	86	2800	38.5	YES	N.A.	YES	ENGINE
300	85	196	3UNF11	219	95	2350	49.0	YES	N.A.	YES	ENGINE
300	85	196	3UNF11	204	88	2600	50.8	YES	N.A.	YES	ENGINE
300	85	196	3UNF11	210	91	2800	42.0	YES	N.A.	YES	ENGINE
300	89	206	3UNF11	220	95	2950	45.0	40	N.A.	40	MOTOR
300	89	206	3UNF11	220	95	3000	45.0	YES	N.A.	YES	ENGINE
300	90	208	3UNF11	219	95	2350	49.0	YES	N.A.	YES	ENGINE
300	90	208	3UNF11	212	92	2600	54.0	YES	N.A.	YES	ENGINE
300	90	208	3UNF11	222	96	2800	46.0	YES	N.A.	YES	ENGINE
300	92	213	3UNF11	219	95	2350	49.0	YES	N.A.	YES	ENGINE
300	95	219	3UNF11	233	101	2950	49.1	50	N.A.	50	MOTOR
300	95	219	3UNF11	227	98	2600	59.4	YES	N.A.	YES	ENGINE
300	95	219	3UNF11	232	100	2800	49.0	YES	N.A.	YES	ENGINE
300	95	219	3UNF11	233	101	3000	49.1	YES	N.A.	YES	ENGINE
300	100	231	2.5UNF8	237	103	2950	53.0	50	N.A.	50	MOTOR
300	100	231	3UNF11	246	106	2950	53.4	50	N.A.	50	MOTOR
300	100	231	3UNF11	235	102	2600	62.8	YES	N.A.	YES	ENGINE
300	100	231	3UNF11	241	104	2800	52.0	YES	N.A.	YES	ENGINE
300	100	231	3UNF11	246	106	3000	53.4	YES	N.A.	YES	ENGINE

Frame Mounted End Suction Fire Pumps



Peerless Pump Company

2005 Dr. Martin Luther King Jr. Street
Indianapolis, IN 46202
Phone: (317) 925-9661 • Fax: (317) 924-7388

US Gpm	Head		Pump Model	Shut-off Head Feet	Shut -Off Head Psi	Speed Rpm	Pump Max Bhp	UL Listed Motor Drive Bhp with 1.15 Serv. Fact. or UL Listed for Engine Drive	ULC Listed Motor Drive Bhp with 1.15 Serv. Fact. or ULC Listed for Engine	FM Approved Motor Drive Bhp with 1.15 Serv. Fact. or FM Approved for Engine	Type Driver
	Psi	Feet									
300	105	242	3UNF11	258	112	2950	57.2	50	N.A.	50	MOTOR
300	105	242	3UNF11	248	107	2600	67.5	YES	N.A.	YES	ENGINE
300	105	242	3UNF11	261	113	2800	58.1	YES	N.A.	YES	ENGINE
300	105	242	3UNF11	258	112	3000	57.2	YES	N.A.	YES	ENGINE
300	110	254	3UNF11	268	116	2950	60.5	60	N.A.	60	MOTOR
300	110	254	3UNF11	265	115	2600	68.0	YES	N.A.	YES	ENGINE
300	110	254	3UNF11	268	116	2800	60.4	YES	N.A.	YES	ENGINE
300	110	254	3UNF11	268	116	3000	60.5	YES	N.A.	YES	ENGINE
300	114	263	3UNF11	265	115	2600	68.0	YES	N.A.	YES	ENGINE
300	115	266	3UNF11	275	119	2950	63.0	60	N.A.	60	MOTOR
300	115	266	3UNF11	294	127	2800	76.0	YES	N.A.	YES	ENGINE
300	115	266	3UNF11	275	119	3000	63.0	YES	N.A.	YES	ENGINE
300	120	277	3UNF11	289	125	2950	68.0	60	N.A.	60	MOTOR
300	120	277	3UNF11	302	131	2800	78.0	YES	N.A.	YES	ENGINE
300	120	277	3UNF11	289	125	3000	68.0	YES	N.A.	YES	ENGINE
300	122	282	2UNF10	240	104	2950	30.0	30	N.A.	30	MOTOR
300	125	289	3UNF11	297	129	2950	71.0	75	N.A.	75	MOTOR
300	125	289	3UNF11	311	135	2800	82.0	YES	N.A.	YES	ENGINE
300	125	289	3UNF11	297	129	3000	71.0	YES	N.A.	YES	ENGINE
300	130	300	3UNF11	319	138	2950	85.0	75	N.A.	75	MOTOR
300	130	300	3UNF11	319	138	3000	85.0	YES	N.A.	YES	ENGINE
300	132	305	3UNF11	311	135	2800	82.0	YES	N.A.	YES	ENGINE
300	135	312	2UNF10	355	154	2950	56.0	50	N.A.	50	MOTOR
300	135	312	3UNF11	327	142	2950	88.0	100	N.A.	100	MOTOR
300	135	312	3UNF11	327	142	3000	88.0	YES	N.A.	YES	ENGINE
300	140	323	3UNF11	345	149	2950	96.0	100	N.A.	100	MOTOR
300	140	323	3UNF11	345	149	3000	96.0	YES	N.A.	YES	ENGINE
300	147	340	3UNF11	345	149	2950	96.0	100	N.A.	100	MOTOR
300	147	340	3UNF11	345	149	3000	96.0	YES	N.A.	YES	ENGINE
400	43	99	3UNF7	125	54	3500	19.0	20	N.A.	20	MOTOR
400	46	106	3UNF8	170	74	2950	30.0	30	N.A.	30	MOTOR
400	52	120	3UNF11	133	58	2350	21.8	YES	N.A.	YES	ENGINE
400	55	127	3UNF11	145	63	2350	24.9	YES	N.A.	YES	ENGINE
400	60	139	3UNF11	158	69	2350	28.3	YES	N.A.	YES	ENGINE
400	62	143	2.5UNF8	130	56	2950	20.0	20	N.A.	20	MOTOR
400	65	150	3UNF11	161	70	2350	32.4	YES	N.A.	YES	ENGINE
400	66	152	3UNF11	165	71	2600	29.0	YES	N.A.	YES	ENGINE
400	70	162	3UNF11	175	76	2350	36.4	YES	N.A.	YES	ENGINE
400	70	162	3UNF11	178	77	2600	30.0	YES	N.A.	YES	ENGINE
400	70	162	3UNF7	190	82	3500	27.0	25	N.A.	25	MOTOR
400	71	164	3UNF8	275	119	2950	42.0	40	N.A.	40	MOTOR
400	75	173	3UNF11	184	80	2350	39.5	YES	N.A.	YES	ENGINE
400	75	173	3UNF11	189	82	2600	32.8	YES	N.A.	YES	ENGINE
400	77	178	3UNF11	193	84	2800	37.0	YES	N.A.	YES	ENGINE
400	80	185	3UNF11	194	84	2350	43.2	YES	N.A.	YES	ENGINE
400	80	185	3UNF11	198	86	2600	48.6	YES	N.A.	YES	ENGINE
400	80	185	3UNF11	204	88	2800	40.1	YES	N.A.	YES	ENGINE
400	85	196	3UNF11	219	95	2350	49.0	YES	N.A.	YES	ENGINE
400	85	196	3UNF11	204	88	2600	50.8	YES	N.A.	YES	ENGINE
400	85	196	3UNF11	228	99	2800	47.5	YES	N.A.	YES	ENGINE
400	86	199	3UNF11	214	93	2950	43.0	40	N.A.	40	MOTOR
400	86	199	3UNF11	214	93	3000	43.0	YES	N.A.	YES	ENGINE
400	90	208	3UNF11	226	98	2950	46.9	50	N.A.	50	MOTOR

Frame Mounted End Suction Fire Pumps



Sterling Fluid Systems (USA), Inc.
Indianapolis, IN 46207-7026



Peerless Pump Company

2005 Dr. Martin Luther King Jr. Street
Indianapolis, IN 46202
Phone: (317) 925-9661 • Fax: (317) 924-7388

US Gpm	Head		Pump Model	Shut-off Head Feet	Shut -Off Head Psi	Speed Rpm	Pump Max Bhp	UL Listed Motor Drive Bhp with 1.15 Serv. Fact. or UL Listed for Engine Drive	ULC Listed Motor Drive Bhp with 1.15 Serv. Fact. or ULC Listed for Engine	FM Approved Motor Drive Bhp with 1.15 Serv. Fact. or FM Approved for Engine	Type Driver
	Psi	Feet									
400	90	208	3UNF11	212	92	2600	54.0	YES	N.A.	YES	ENGINE
400	90	208	3UNF11	232	100	2800	49.0	YES	N.A.	YES	ENGINE
400	90	208	3UNF11	226	98	3000	46.9	YES	N.A.	YES	ENGINE
400	91	210	3UNF11	219	95	2350	49.0	YES	N.A.	YES	ENGINE
400	95	219	3UNF11	233	101	2950	49.1	50	N.A.	50	MOTOR
400	95	219	3UNF11	227	98	2600	59.4	YES	N.A.	YES	ENGINE
400	95	219	3UNF11	241	104	2800	52.0	YES	N.A.	YES	ENGINE
400	95	219	3UNF11	233	101	3000	49.1	YES	N.A.	YES	ENGINE
400	97	224	2.5UNF8	237	103	2950	53.0	50	N.A.	50	MOTOR
400	100	231	3UNF11	246	106	2950	53.4	50	N.A.	50	MOTOR
400	100	231	3UNF11	235	102	2600	62.8	YES	N.A.	YES	ENGINE
400	100	231	3UNF11	248	107	2800	53.7	YES	N.A.	YES	ENGINE
400	100	231	3UNF11	246	106	3000	53.4	YES	N.A.	YES	ENGINE
400	105	242	3UNF11	258	112	2950	57.2	50	N.A.	50	MOTOR
400	105	242	3UNF11	248	107	2600	67.5	YES	N.A.	YES	ENGINE
400	105	242	3UNF11	261	113	2800	58.1	YES	N.A.	YES	ENGINE
400	105	242	3UNF11	258	112	3000	57.2	YES	N.A.	YES	ENGINE
400	110	254	3UNF11	275	119	2950	63.0	60	N.A.	60	MOTOR
400	110	254	3UNF11	265	115	2600	68.0	YES	N.A.	YES	ENGINE
400	110	254	3UNF11	274	119	2800	63.0	YES	N.A.	YES	ENGINE
400	110	254	3UNF11	275	119	3000	63.0	YES	N.A.	YES	ENGINE
400	112	259	3UNF11	265	115	2600	68.0	YES	N.A.	YES	ENGINE
400	115	266	3UNF11	282	122	2950	65.0	60	N.A.	60	MOTOR
400	115	266	3UNF11	294	127	2800	76.0	YES	N.A.	YES	ENGINE
400	115	266	3UNF11	282	122	3000	65.0	YES	N.A.	YES	ENGINE
400	120	277	3UNF11	289	125	2950	68.0	60	N.A.	60	MOTOR
400	120	277	3UNF11	302	131	2800	78.0	YES	N.A.	YES	ENGINE
400	120	277	3UNF11	289	125	3000	68.0	YES	N.A.	YES	ENGINE
400	125	289	3UNF11	297	129	2950	71.0	75	N.A.	75	MOTOR
400	125	289	3UNF11	311	135	2800	82.0	YES	N.A.	YES	ENGINE
400	125	289	3UNF11	297	129	3000	71.0	YES	N.A.	YES	ENGINE
400	130	300	3UNF11	319	138	2950	85.0	75	N.A.	75	MOTOR
400	130	300	3UNF11	311	135	2800	82.0	YES	N.A.	YES	ENGINE
400	130	300	3UNF11	319	138	3000	85.0	YES	N.A.	YES	ENGINE
400	135	312	3UNF11	335	145	2950	92.0	100	N.A.	100	MOTOR
400	135	312	3UNF11	335	145	3000	92.0	YES	N.A.	YES	ENGINE
400	140	323	3UNF11	345	149	2950	96.0	100	N.A.	100	MOTOR
400	140	323	3UNF11	345	149	3000	96.0	YES	N.A.	YES	ENGINE
400	145	334	3UNF11	345	149	2950	96.0	100	N.A.	100	MOTOR
400	145	334	3UNF11	345	149	3000	96.0	YES	N.A.	YES	ENGINE
450	40	92	3UNF7	125	54	3500	19.0	20	N.A.	20	MOTOR
450	44	102	3UNF8	170	74	2950	30.0	30	N.A.	30	MOTOR
450	50	115	3UNF11	133	58	2350	22.0	YES	N.A.	YES	ENGINE
450	55	127	3UNF11	145	63	2350	25.0	YES	N.A.	YES	ENGINE
450	60	139	3UNF11	162	70	2350	29.5	YES	N.A.	YES	ENGINE
450	63	145	3UNF11	165	71	2600	29.0	YES	N.A.	YES	ENGINE
450	65	150	3UNF11	170	74	2350	35.1	YES	N.A.	YES	ENGINE
450	65	150	3UNF11	173	75	2600	29.5	YES	N.A.	YES	ENGINE
450	67	155	3UNF7	190	82	3500	27.0	25	N.A.	25	MOTOR
450	68	157	3UNF8	275	119	2950	42.0	40	N.A.	40	MOTOR
450	70	162	3UNF11	184	80	2350	39.5	YES	N.A.	YES	ENGINE
450	70	162	3UNF11	183	79	2600	31.3	YES	N.A.	YES	ENGINE
450	75	173	3UNF11	198	86	2350	44.1	YES	N.A.	YES	ENGINE

Frame Mounted End Suction Fire Pumps



Sterling Fluid Systems (USA), Inc.
Indianapolis, IN 46207-7026



Peerless Pump Company

2005 Dr. Martin Luther King Jr. Street
Indianapolis, IN 46202
Phone: (317) 925-9661 • Fax: (317) 924-7388

US Gpm	Head		Pump Model	Shut-off Head Feet	Shut -Off Head Psi	Speed Rpm	Pump Max Bhp	UL Listed Motor Drive Bhp with 1.15 Serv. Fact. or UL Listed for Engine Drive	ULC Listed Motor Drive Bhp with 1.15 Serv. Fact. or ULC Listed for Engine	FM Approved Motor Drive Bhp with 1.15 Serv. Fact. or FM Approved for Engine	Type Driver
	Psi	Feet									
450	75	173	3UNF11	196	85	2600	39.0	YES	N.A.	YES	ENGINE
450	75	173	3UNF11	198	86	2800	38.5	YES	N.A.	YES	ENGINE
450	80	185	3UNF11	219	95	2350	49.0	YES	N.A.	YES	ENGINE
450	80	185	3UNF11	198	86	2600	48.6	YES	N.A.	YES	ENGINE
450	80	185	3UNF11	210	91	2800	42.0	YES	N.A.	YES	ENGINE
450	84	194	3UNF11	214	93	2950	43.0	40	N.A.	40	MOTOR
450	84	194	3UNF11	214	93	3000	43.0	YES	N.A.	YES	ENGINE
450	85	196	3UNF11	219	95	2350	49.0	YES	N.A.	YES	ENGINE
450	85	196	3UNF11	204	88	2600	50.8	YES	N.A.	YES	ENGINE
450	85	196	3UNF11	222	96	2800	46.0	YES	N.A.	YES	ENGINE
450	88	203	3UNF11	219	95	2350	49.0	YES	N.A.	YES	ENGINE
450	90	208	3UNF11	226	98	2950	46.9	50	N.A.	50	MOTOR
450	90	208	3UNF11	215	93	2600	55.0	YES	N.A.	YES	ENGINE
450	90	208	3UNF11	232	100	2800	49.0	YES	N.A.	YES	ENGINE
450	90	208	3UNF11	226	98	3000	46.9	YES	N.A.	YES	ENGINE
450	95	219	3UNF11	233	101	2950	49.1	50	N.A.	50	MOTOR
450	95	219	3UNF11	227	98	2600	59.4	YES	N.A.	YES	ENGINE
450	95	219	3UNF11	241	104	2800	52.0	YES	N.A.	YES	ENGINE
450	95	219	3UNF11	233	101	3000	49.1	YES	N.A.	YES	ENGINE
450	100	231	3UNF11	246	106	2950	55.6	50	N.A.	50	MOTOR
450	100	231	3UNF11	238	103	2600	64.1	YES	N.A.	YES	ENGINE
450	100	231	3UNF11	254	110	2800	55.8	YES	N.A.	YES	ENGINE
450	100	231	3UNF11	246	106	3000	55.6	YES	N.A.	YES	ENGINE
450	105	242	3UNF11	258	112	2950	60.5	60	N.A.	60	MOTOR
450	105	242	3UNF11	248	107	2600	67.5	YES	N.A.	YES	ENGINE
450	105	242	3UNF11	268	116	2800	60.4	YES	N.A.	YES	ENGINE
450	105	242	3UNF11	258	112	3000	60.5	YES	N.A.	YES	ENGINE
450	110	254	3UNF11	275	119	2950	62.8	60	N.A.	60	MOTOR
450	110	254	3UNF11	294	127	2800	76.0	YES	N.A.	YES	ENGINE
450	110	254	3UNF11	275	119	3000	62.8	YES	N.A.	YES	ENGINE
450	111	256	3UNF11	265	115	2600	68.0	YES	N.A.	YES	ENGINE
450	115	266	3UNF11	282	122	2950	65.0	60	N.A.	60	MOTOR
450	115	266	3UNF11	302	131	2800	78.0	YES	N.A.	YES	ENGINE
450	115	266	3UNF11	282	122	3000	65.0	YES	N.A.	YES	ENGINE
450	120	277	3UNF11	289	125	2950	71.0	75	N.A.	75	MOTOR
450	120	277	3UNF11	311	135	2800	82.0	YES	N.A.	YES	ENGINE
450	120	277	3UNF11	289	125	3000	71.0	YES	N.A.	YES	ENGINE
450	125	289	3UNF11	297	129	2950	85.0	75	N.A.	75	MOTOR
450	125	289	3UNF11	311	135	2800	82.0	YES	N.A.	YES	ENGINE
450	125	289	3UNF11	297	129	3000	85.0	YES	N.A.	YES	ENGINE
450	129	299	3UNF11	311	135	2800	82.0	YES	N.A.	YES	ENGINE
450	130	300	3UNF11	319	138	2950	88.0	100	N.A.	100	MOTOR
450	130	300	3UNF11	319	138	3000	88.0	YES	N.A.	YES	ENGINE
450	135	312	3UNF11	335	145	2950	92.0	100	N.A.	100	MOTOR
450	135	312	3UNF11	335	145	3000	92.0	YES	N.A.	YES	ENGINE
450	140	323	3UNF11	345	149	2950	96.0	100	N.A.	100	MOTOR
450	140	323	3UNF11	345	149	3000	96.0	YES	N.A.	YES	ENGINE
450	144	333	3UNF11	345	149	2950	96.0	100	N.A.	100	MOTOR
450	144	333	3UNF11	345	149	3000	96.0	YES	N.A.	YES	ENGINE
500	50	115	3UNF11	133	58	2350	22.0	YES	N.A.	YES	ENGINE
500	55	127	3UNF11	145	63	2350	25.0	YES	N.A.	YES	ENGINE
500	60	139	3UNF11	162	70	2350	29.5	YES	N.A.	YES	ENGINE
500	61	141	3UNF11	165	71	2600	29.0	YES	N.A.	YES	ENGINE

Frame Mounted End Suction Fire Pumps



Sterling Fluid Systems (USA), Inc.
Indianapolis, IN 46207-7026



Peerless Pump Company

2005 Dr. Martin Luther King Jr. Street
Indianapolis, IN 46202
Phone: (317) 925-9661 • Fax: (317) 924-7388

US Gpm	Head		Pump Model	Shut-off Head Feet	Shut -Off Head Psi	Speed Rpm	Pump Max Bhp	UL Listed Motor Drive Bhp with 1.15 Serv. Fact. or UL Listed for Engine Drive	ULC Listed Motor Drive Bhp with 1.15 Serv. Fact. or ULC Listed for Engine	FM Approved Motor Drive Bhp with 1.15 Serv. Fact. or FM Approved for Engine	Type Driver
	Psi	Feet									
500	65	150	3UNF11	170	74	2350	35.1	YES	N.A.	YES	ENGINE
500	65	150	3UNF11	178	77	2600	30.0	YES	N.A.	YES	ENGINE
500	70	162	3UNF11	184	80	2350	39.5	YES	N.A.	YES	ENGINE
500	70	162	3UNF11	189	82	2600	32.8	YES	N.A.	YES	ENGINE
500	72	166	3UNF11	188	81	2800	35.0	YES	N.A.	YES	ENGINE
500	75	173	3UNF11	198	86	2350	44.1	YES	N.A.	YES	ENGINE
500	75	173	3UNF11	194	84	2600	39.0	YES	N.A.	YES	ENGINE
500	75	173	3UNF11	204	88	2800	40.1	YES	N.A.	YES	ENGINE
500	80	185	3UNF11	219	95	2350	49.0	YES	N.A.	YES	ENGINE
500	80	185	3UNF11	198	86	2600	48.6	YES	N.A.	YES	ENGINE
500	80	185	3UNF11	222	96	2800	46.0	YES	N.A.	YES	ENGINE
500	82	189	3UNF11	207	90	2950	41.0	40	N.A.	40	MOTOR
500	82	189	3UNF11	207	90	3000	41.0	YES	N.A.	YES	ENGINE
500	85	196	3UNF11	220	95	2950	45.0	40	N.A.	40	MOTOR
500	85	196	3UNF11	219	95	2350	49.0	YES	N.A.	YES	ENGINE
500	85	196	3UNF11	210	91	2600	52.9	YES	N.A.	YES	ENGINE
500	85	196	3UNF11	232	100	2800	49.0	YES	N.A.	YES	ENGINE
500	85	196	3UNF11	220	95	3000	45.0	YES	N.A.	YES	ENGINE
500	85	196	6UNF12	200	87	2600	75.0	YES	N.A.	YES	ENGINE
500	88	203	3UNF11	219	95	2350	49.0	YES	N.A.	YES	ENGINE
500	90	208	3UNF11	233	101	2950	49.1	50	N.A.	50	MOTOR
500	90	208	3UNF11	221	95	2600	57.1	YES	N.A.	YES	ENGINE
500	90	208	3UNF11	241	104	2800	52.0	YES	N.A.	YES	ENGINE
500	90	208	3UNF11	233	101	3000	49.1	YES	N.A.	YES	ENGINE
500	95	219	3UNF11	246	106	2950	53.4	50	N.A.	50	MOTOR
500	95	219	3UNF11	233	101	2600	61.9	YES	N.A.	YES	ENGINE
500	95	219	3UNF11	248	107	2800	53.7	YES	N.A.	YES	ENGINE
500	95	219	3UNF11	246	106	3000	53.4	YES	N.A.	YES	ENGINE
500	98	226	6UNF12	230	100	2800	100.0	YES	N.A.	YES	ENGINE
500	100	231	3UNF11	258	112	2950	57.2	50	N.A.	50	MOTOR
500	100	231	3UNF11	243	105	2600	66.1	YES	N.A.	YES	ENGINE
500	100	231	3UNF11	261	113	2800	58.1	YES	N.A.	YES	ENGINE
500	100	231	3UNF11	258	112	3000	57.2	YES	N.A.	YES	ENGINE
500	105	242	3UNF11	268	116	2950	60.5	60	N.A.	60	MOTOR
500	105	242	3UNF11	265	115	2600	68.0	YES	N.A.	YES	ENGINE
500	105	242	3UNF11	274	119	2800	63.0	YES	N.A.	YES	ENGINE
500	105	242	3UNF11	268	116	3000	60.5	YES	N.A.	YES	ENGINE
500	108	250	3UNF11	265	115	2600	68.0	YES	N.A.	YES	ENGINE
500	108	249	6UNF12	260	113	2950	120.0	125	N.A.	125	MOTOR
500	110	254	3UNF11	271	117	2950	61.7	60	N.A.	60	MOTOR
500	110	254	3UNF11	294	127	2800	76.0	YES	N.A.	YES	ENGINE
500	110	254	3UNF11	271	117	3000	61.7	YES	N.A.	YES	ENGINE
500	112	259	6UNF12	268	116	3000	125.0	YES	N.A.	YES	ENGINE
500	115	266	3UNF11	275	119	2950	63.0	60	N.A.	60	MOTOR
500	115	266	3UNF11	302	131	2800	78.0	YES	N.A.	YES	ENGINE
500	115	266	3UNF11	275	119	3000	63.0	YES	N.A.	YES	ENGINE
500	120	277	3UNF11	282	122	2950	65.2	60	N.A.	60	MOTOR
500	120	277	3UNF11	311	135	2800	82.0	YES	N.A.	YES	ENGINE
500	120	277	3UNF11	282	122	3000	65.2	YES	N.A.	YES	ENGINE
500	125	289	3UNF11	297	129	2950	71.0	75	N.A.	75	MOTOR
500	125	289	3UNF11	311	135	2800	82.0	YES	N.A.	YES	ENGINE
500	125	289	3UNF11	297	129	3000	71.0	YES	N.A.	YES	ENGINE
500	127	293	3UNF11	311	135	2800	82.0	YES	N.A.	YES	ENGINE

Frame Mounted End Suction Fire Pumps



Sterling Fluid Systems (USA), Inc.
Indianapolis, IN 46207-7026



Peerless Pump Company

2005 Dr. Martin Luther King Jr. Street
Indianapolis, IN 46202
Phone: (317) 925-9661 • Fax: (317) 924-7388

US Gpm	Head		Pump Model	Shut-off Head Feet	Shut -Off Head Psi	Speed Rpm	Pump Max Bhp	UL Listed Motor Drive Bhp with 1.15 Serv. Fact. or UL Listed for Engine Drive	ULC Listed Motor Drive Bhp with 1.15 Serv. Fact. or ULC Listed for Engine	FM Approved Motor Drive Bhp with 1.15 Serv. Fact. or FM Approved for Engine	Type Driver
	Psi	Feet									
500	130	300	3UNF11	327	142	2950	88.0	100	N.A.	100	MOTOR
500	130	300	3UNF11	327	142	3000	88.0	YES	N.A.	YES	ENGINE
500	135	312	3UNF11	335	145	2950	92.0	100	N.A.	100	MOTOR
500	135	312	3UNF11	335	145	3000	92.0	YES	N.A.	YES	ENGINE
500	138	319	6UNF12	325	141	2800	172.0	YES	N.A.	YES	ENGINE
500	140	323	3UNF11	345	149	2950	96.0	100	N.A.	100	MOTOR
500	140	323	3UNF11	345	149	3000	96.0	YES	N.A.	YES	ENGINE
500	142	328	3UNF11	345	149	2950	96.0	100	N.A.	100	MOTOR
500	142	328	3UNF11	345	149	3000	96.0	YES	N.A.	YES	ENGINE
500	149	344	6UNF12	345	149	2600	199.0	YES	N.A.	YES	ENGINE
500	154	356	6UNF12	360	156	2950	202.0	200	N.A.	200	MOTOR
500	159	367	6UNF12	375	162	3000	212.0	YES	N.A.	YES	ENGINE
750	83	192	6UNF12	200	87	2600	75.0	YES	N.A.	YES	ENGINE
750	97	224	6UNF12	230	100	2800	100.0	YES	N.A.	YES	ENGINE
750	107	247	6UNF12	260	113	2950	120.0	125	N.A.	125	MOTOR
750	111	256	6UNF12	268	116	3000	125.0	YES	N.A.	YES	ENGINE
750	137	316	6UNF12	325	141	2800	172.0	YES	N.A.	YES	ENGINE
750	148	342	6UNF12	345	149	2600	199.0	YES	N.A.	YES	ENGINE
750	153	353	6UNF12	360	156	2950	202.0	200	N.A.	200	MOTOR
750	158	365	6UNF12	375	162	3000	212.0	YES	N.A.	YES	ENGINE
1000	79	182	6UNF12	200	87	2600	75.0	YES	N.A.	YES	ENGINE
1000	95	219	6UNF12	230	100	2800	100.0	YES	N.A.	YES	ENGINE
1000	106	245	6UNF12	260	113	2950	120.0	125	N.A.	125	MOTOR
1000	110	254	6UNF12	268	116	3000	125.0	YES	N.A.	YES	ENGINE
1000	136	314	6UNF12	325	141	2800	172.0	YES	N.A.	YES	ENGINE
1000	145	335	6UNF12	345	149	2600	199.0	YES	N.A.	YES	ENGINE
1000	152	351	6UNF12	360	156	2950	202.0	200	N.A.	200	MOTOR
1000	157	363	6UNF12	375	162	3000	212.0	YES	N.A.	YES	ENGINE
1250	74	171	6UNF12	200	87	2600	75.0	YES	N.A.	YES	ENGINE
1250	89	206	6UNF12	230	100	2800	100.0	YES	N.A.	YES	ENGINE
1250	101	233	6UNF12	260	113	2950	120.0	125	N.A.	125	MOTOR
1250	105	243	6UNF12	268	116	3000	125.0	YES	N.A.	YES	ENGINE
1250	132	305	6UNF12	325	141	2800	172.0	YES	N.A.	YES	ENGINE
1250	142	328	6UNF12	345	149	2600	199.0	YES	N.A.	YES	ENGINE
1250	149	344	6UNF12	360	156	2950	202.0	200	N.A.	200	MOTOR
1250	154	356	6UNF12	375	162	3000	212.0	YES	N.A.	YES	ENGINE
1500	80	185	6UNF12	230	100	2800	100.0	YES	N.A.	YES	ENGINE
1500	95	219	6UNF12	260	113	2950	120.0	125	N.A.	125	MOTOR
1500	99	229	6UNF12	268	116	3000	125.0	YES	N.A.	YES	ENGINE
1500	127	293	6UNF12	325	141	2800	172.0	YES	N.A.	YES	ENGINE
1500	144	333	6UNF12	360	156	2950	202.0	200	N.A.	200	MOTOR
1500	150	347	6UNF12	375	162	3000	212.0	YES	N.A.	YES	ENGINE