

# PACO LCS

End Suction Split-Coupled pump that's simple, compact, and efficient



---


## Key Benefits:

- 35% smaller foot print over frame mount design
  - Eliminates coupling alignment requirements, laser alignment costs and faster installation
  - No baseplate grouting required
  - Service friendly design allows rapid mechanical seal access without motor removal, thus reducing maintenance cost
  - Lower weight offers installation ease
- 

For consulting engineers, visit **GrundfosExpress.com** for technical information. For Grundfos sales and distributors, visit **GrundfosExpressSuite.com**

**[www.grundfos.us/LCS](http://www.grundfos.us/LCS)**

# PACO LCS Technical Data



Visit [grundfosexpresssuite.com](http://grundfosexpresssuite.com)

	PACO LCS
Flow, Q	10 to 4200 gpm
Head, H	15 to 430 ft
Fluid temp.	10° to 275° F
Max. working pressure	175 psi*
HP range	3 to 125 hp
Speed	3600, 1800, and 1200 RPM
Discharge/Suction sizes	1.25 to 8 in.

\* 250 psi rating available

L-LCS-SL-01 07-14 (US)

**GRUNDFOS CBS Inc.**  
902 Koomey Road  
Brookshire, TX 77423  
Phone: (281) 994-2700  
Fax: (559) 347-2702

**GRUNDFOS Canada**  
2941 Brighton Road  
Oakville, Ontario  
L6H 6C9  
Phone: (905) 829-9533  
Fax: (905) 829-9512

**GRUNDFOS Mexico**  
Boulevard TLC No. 15  
Parque Industrial Stiva Aeropuerto  
C.P. 66600 Apodaca, N.L. Mexico  
Phone: 011-52-81-8144 4000  
Fax: 011-52-81-8144 4010

[www.grundfos.us](http://www.grundfos.us)

The name Grundfos, the Grundfos logo, and be think innovate are registered trademarks owned by Grundfos Holding A/S or Grundfos A/S, Denmark. All rights reserved worldwide.

**GRUNDFOS**