


Horizontal Split Case Pump

PACO KP

Built to deliver up to 20,000 gallons-per-minute, this high capacity single stage pump is ideal for demanding applications. The KP features compact, robust bearing housing with a 360-degree machined register fit, which limits shaft deflection and optimizes alignment.

Available in a wide range of material options, the KP is highly customizable and perfect for specialized, challenging applications.



Key Features and Benefits


- Hydraulic double volute design reduces radial loads, internal recirculation and turbulence, resulting in a longer pump life span and a higher operation efficiency
- Axially split design allows for quick removal of the top casing and access to pump components (bearings, wear rings, impeller, and shaft seal) without disturbing the motor or pipe work, saving time and money
- Standard bronze wear rings protect pump from erosion and permit simple maintenance of proper running clearances
- Horizontal, space saving design eliminates need for distance around pump for maintenance access
- Highly customizable construction including choices of case material with numerous impeller and shaft seal options
- Integrally cast suction baffles reduce suction recirculation loss and ensure even flow distribution and quiet, vibration-free operation. Suction chamber inlet configuration also increases hydraulic efficiency and lowers net positive suction head requirements
- Independent bearing housing design allows access to the pump components without removing the top half of the casing
- Extended pump range up to 20,000 gallons-per-minute to serve all your high flow applications
- Francis Vane Impeller design with extended vanes and enlarged eye increases efficiency and reduces vibration and noise
- Certified to NSF/ANSI 50 and NSF/ANSI 61

APPLICATIONS

- Chilled water
- Condensed water
- Service water
- District energy
- Water distribution
- Central plant heating/cooling

KP Technical Data

KP Information	
Flow, Q:	max. 20,000 gpm
Head, H:	max. 700 feet
Fluid temperature:	-20° to 275° F
Working pressure:	max. 400 psi
HP range:	max. 2000 Hp
Discharge sizes:	2 to 20 in.
Impellers:	7 to 24 in.
Approvals	Certified to NSF/ANSI 50 and NSF/ANSI 61



The name Grundfos, the Grundfos logo, and be think innovate are registered trademarks owned by Grundfos Holding A/S or Grundfos A/S, Denmark. All rights reserved worldwide. L-KP-SL-001 11-17